



AquapHyll™ Portable Plus

Easy to Use

User friendly design

Dilution control in your hands

- 1 Shift control selector lets you switch between bottle-fill and bucket-fill flow rates.
- 2 Twist on connector for closed loop chemical bottle tops.
- 3 Twist on connector (3/4" GHT) for water source hose.
- 4 Discharge tube for easy dispensing of liquid.
- 5 Ergonomic squeeze handle eliminates hand fatigue.
- 6 Red lock On/Off ring allows user hands free filling and eliminates accidental activation.
- 7 High quality plastic construction stands up to daily wear and tear.



RECOMMENDED PRODUCTS



AquapHyll Quad, our accurate chemical metering cabinet, creates a fast, versatile and durable support system for any janitor's closet.



Pioneer Eclipse offers concentrated cleaners, maintainers, degreasers and germicides designed to operate effectively with the AquapHyll™ Chemical Dispensing Systems.

TECHNICAL DATA

Flow Rates	Bottle: 1.0 GPM (3,8 liters) Bucket: 3.5 GPM (13,25 liters)
Dimensions	11" x 4.5" x 2"
Operational Pressure	20 – 90
Range (psi):	
Operational Temperature	40° – 120°
Range (°F)	

AVAILABLE MODELS

MASLID-1: AquapHyll Portable Plus
Handheld Dispenser

